




Aspirant and
filtering hood

GS 60



Applications

For the uptake of chemicals harmful to health, suitable for services anatomy, outpatient, operating rooms, withdrawals centers, classrooms university.

Aspiration filtering

Vacuum module filtering suspended to ceiling Recirculating environment or expulsion of the filtered air, filtered on pre-filter and activated carbon filter dim 1cm60xpcm45xhcm10 specific to the pollutant to be treated.

Structures

Structure in steel sheet coated EPOSSIEPOIESTERE, suction flow mc / h 450/700 adjustable, noise inf.60 db, power V230-50HZ-150W-0.6A, electrical protection IP44, switching with IR command, hour counter, LED lighting 600 Lux / 1mt, suspended ceiling.

Dimensions

External dimensions (LxPxH): cm 100x75x60

Accessories

Spy alarm insufficient flow.

Certifications

The cabinets offered are marked CE - 2006/42 - 2006/95 CEE - 2004/108 CEE CEI EN 61010 CEI 66.5.

COMFIT s.r.l

Via Viberti, 4

10141 Torino TO

Tel. +39011 720085

Fax.+39011 728870

comfit@tiscali.it

www.comfit.org

Con riserva di modifica senza preavviso delle caratteristiche tecniche dei prodotti illustrati. Tutti i diritti riservati. COMFIT sas. 05/2014

Aria nuova in laboratorio...